# **OMB** 502UNI



# **UNIVERSAL BARGRAPH**

- Three-color bargraph 2x 50 LED
- Two-channel design
- Multifunction input (PM, OHM, RTD, DU)
- Digital filters, Linearization
- Size of DIN 144 x 48 mm
- Power supply 10...30 V AC/DC; 80...250 V AC/DC
- Option Comparators

# **OMB** 502UNI



The OMB 200/300/500UNI model series are simple bargraphs designed for maximum efficiency and user comfort while maintaining their favourable price. Type OMB 502UNI is a multifunction instrument with the option of configuration for 5 various input options, easily configurable in the instrument menu.

The instrument is based on a single-chip microcontroller with an A/D converter, which secures good accuracy, stability and easy operation of the instrument.

By selecting the insertion mode of the front plexiglass (reverse/face) you may choose the required scale printing for vertical or horizontal design of the

#### **OMB** 502UNI

PROCESS MONITOR OHMMETER THERMOMETER FOR Pt/Ni DISPLAY UNIT FOR LINEAR POTENTIOMETERS

# **OPERATION**

The instrument is set and controlled by five buttons located under the front panel. All programmable settings of the instrument may be performed in two adjusting

LIGHT MENU contains solely items necessary for instrument setting.

PROFI MENU contains complete instrument setting, which is accessible only via OM Link

Standard equipment is the OM Link interface, which together with the operation program enables modification and filing of all instrument settings as well as performing firmware updates (with OML cable).

All settings are stored in the EEPROM memory (settings hold even after the instrument is switched off).

#### OPTION

**COMPARATORS** are assigned to monitor one or two limit values with relay output. The limit has adjustable hysteresis within full range of the display and selectable delay of the switch-on within the range of 0...99 s. Reaching the preset limits is signalled by LED and simultaneously by the switch-on of the relevant relay.

# STANDARD FUNCTIONS

## PROGRAMMABLE PROJECTION

Selection: of input type and measuring range

Setting: manual, in menu optional projection on the display may be set for both limit values of the input signal

Projection: 50 LED

#### FUNCTIONS

Linearization: non-linear signals can be linearized by the means of a linearization table (up to 25 points)

#### DIGITAL FILTERS

Exponential average: from 2...100 measurements Rounding: setting the projection step for display

# EXTERNAL CONTROL

Hold: display/instrument blocking Lock: control keys blocking

### TECHNICAL DATA

Number inputs		2				
РМ	Range	optional in configuration menu				
		020 m/	A < 1,2 V	Input		
		420 m/	A < 1,2 V	Input		
		02 V	182 kΩ	Input 2		
		05 V	182 kΩ	Input 2		
		010 V	182 kΩ	Input 2		
ОНМ	Range	optional in configuration menu $0100~k\Omega$				
	Connection	2 wire				
Pt	Туре	optional in configuration menu				
		EU > 100	-50°450°C			
	Connection	2 wire				
Ni	Туре	optional in configuration menu				
		Ni 1 000	-50°250°C			
	Connection	2 wire				
DU	Pot. power supply	2,5 VDC/6 mA, Potentiometer resistance > 500 $\Omega$				
External input		1 input, on contact				
		The follo	owing functions can be	assigned:		
		OFF	input off			
		HOLD	display stop			
		LOCK	control keys blocking			

#### PROJECTION

Display: 2x 50 LED Bar color: red/green/orange
Decimal point: adjustable - in menu Brightness: adjustable - in menu

#### INSTRUMENT ACCURACY

TC: 50 ppm/°C

Accuracy: ±1% of range + 1 digit Rate: 0,5/5/50/max. measurement/s

Overload capacity: 2x; 10x (t < 30 ms) Line compensation: max. 30  $\Omega$  (RTD)

Linearization: linear interpolation in 25 points (only via OM Link) Digital filters: exponential average, rounding

OM Link: company communication interface for operation, setting and update of instruments

Watch-dog: reset after 25 ms Calibration: at 25°C and 40 % r.h.

# COMPARATOR

Type: digital, menu adjustable, contact switch-on < 50 ms

Hysteresis mode: switching limit, hysteresis band (Lim and  $\pm 1/2$  Hys.) and time ( $\pm 99.9$  s) determining the switching delay

Output: 1...2x relays Form A (250 VAC/30 VDC, 3 A);

1...2x open collector (30 VDC/100 mA)

#### POWER SUPPLY

Range: 10...30 V AC/DC, ±10 %, PF≥0.4, I<sub>STP</sub>< 45 A/1 ms, isolated 80...250 V AC/DC, ±10 %, PF≥0.4, I<sub>STP</sub>< 45 A/1 ms, isolated

Consumption: < 5,0 W/5,4 VA

Power supply is protected by a fuse inside the instrument.

#### MECHANIC PROPERTIES

Material: Noryl GFN2 SE1, incombustible UL 94 V-I Dimensions: 144 x 48 x 75 mm (w x h x d) Panel cutout: 138 x 43,5 mm (w x h)

#### OPERATING CONDITIONS

Connection: connector terminal blocks, section < 1,5/2,5 mm<sup>2</sup>
Stabilization period: within 5 minutes after switch-on

Working temperature: -20°...60°C Storage temperature: -20°...85°C


Protection: IP40 (front panel only) El. safety: EN 61010-1, A2

Dielectric strength: 4 kVAC per 1 min test between supply and input 4 kVAC per 1 min test between input and relay output Insulation resistance: for pollution degree II, measuring cat. III power supply > 300 V (PI)

input, output > 300 V (PI), 150 V (DI) EMC: EN 61326-1

PI - Primary insulation, DI - Double insulation

# CONNECTION



# ORDER CODE

OKDER GODE								
OMB 502	UNI -							
Power supply	1030 V AC/DC	0						
	80250 V AC/DC	1						
Comparators	no		0					
	1x relay (Form A)		1					
	2x relay (Form A)		2					
	1x open collector		3					
	2x open collector		4					
Specification	customized version, do not fill in			00				

Basic configuration of the instrument is indicated in bold.